

Corning® Centrifuge Tubes

Designed for Optimum Performance

Corning offers a full line of disposable, premium quality conical centrifuge tubes manufactured from high quality, ultra-clear resins. These tubes meet the quality and performance standards demanded by researchers.

► **High Speed 15 mL and 50 mL tubes**

- Rated up to 17,000 RCF
- 95 kPA (14 psi) pressure-tested (plug seal cap)
- RNase-/DNase-free
- Nonpyrogenic
- Sterile

► **Large Volume 250 mL and 500 mL tubes**

- Ideal for large volume centrifugation
- Best choice for cell harvesting and purification
- Nonpyrogenic
- Sterile

► **Simplify your workflow with:**

- Color bands visually identify samples
- Hazardous materials pictograms that comply with OSHA and GHS standards



Ordering Information

Corning® 15 mL Centrifuge Tubes



Easy ID color strip tubes

Fisher Scientific Cat. No.	Corning Cat. No.	Material	Cap Style	Max. RCF	Feature	Qty/Pk	Qty/Cs
05-538-51A	430053	PET	Plug seal	3,600	Conical bottom	25/sleeve	500
05-538-1	430055	PET	Plug seal	3,600	Conical bottom	50/rack	500
05-538-53D	430052	PP	Plug seal	12,000	Conical bottom	50/rack	500
05-538-53F	430766	PP	Plug seal	12,000	Conical bottom	25/sleeve	500
05-538-59A	430790	PP	CentriStar™	12,500	Conical bottom	50/rack	500
05-538-59B	430791	PP	CentriStar	12,500	Conical bottom	25/sleeve	500

Corning 50 mL Centrifuge Tubes



50 mL centrifuge tube with hazardous materials label

05-538-49	430304	PET	Plug seal	3,600	Conical bottom	25/rack	500	
05-538-55	430290	PP	Plug seal	15,500	Conical bottom	25/rack	500	
05-538-55A	430291	PP	Plug seal	15,500	Conical bottom	25/sleeve	500	
05-526-B	430828	PP	CentriStar	17,000	Conical bottom	25/rack	500	
05-538-60	430829	PP	CentriStar	17,000	Conical bottom	25/sleeve	500	
07-203-510	4558	PP	CentriStar conical bottom	17,000	Conical bottom	25/Universal rack*	300	
New	07-201-991	431526	PP	Plug seal	15,500	Easy ID color strip - green, conical bottom	25/Universal rack*	300
New	07-201-992	431527	PP	Plug seal	15,500	Easy ID color strip - orange, conical bottom	25/Universal rack*	300
New	07-201-993	431528	PP	Plug seal	15,500	Easy ID color strip - blue, conical bottom	25/Universal rack*	300
New	07-201-990	431525	PP	Plug seal	15,500	Hazardous materials label, conical bottom	25/Universal rack*	300
05-538-67	430897	PP	Plug seal	3,000	Self-standing bottom	25/sleeve	500	
05-538-68	430921	PP	CentriStar	3,000	Self-standing bottom	25/sleeve	500	

*New innovative universal rack can hold 50 mL and 15 mL tubes securely, allowing researchers to work with and store both size tubes in the same rack, saving bench and storage space.

250 mL and 500 mL Premium Quality Centrifuge Tubes and Support Cushions

Fisher Scientific Cat. No.	Corning Cat. No.	Description	Material	Cap Style	Max RCF	Qty/Pk	Qty/Cs
05-538-53	430776	250 mL tube	PP	Plug seal	6,000	6	102
05-538-53A	430236	250 mL support cushion*	PEI	n/a	n/a	n/a	6
07-200-621	431123	500 mL tube	PP	Plug seal	6,000	6	36
07-200-622	431124	500 mL support cushion*	PEI	n/a	n/a	n/a	6

*Support cushions must be used with the 250 mL and 500 mL centrifuge tubes unless the rotor has appropriately shaped V-bottom holders. PP = Polypropylene, PET = Polyethylene Terephthalate, RCF = Relative Centrifugal Force (x g), PEI = Polyetherimide

Warranty/Disclaimer: Unless otherwise specified, all products are for research use only. Not intended for use in diagnostic or therapeutic procedures. Corning Life Sciences makes no claims regarding the performance of these products for clinical or diagnostic applications.

CORNING | **FALCON** | **AXYGEN** | **GOSELIN** | **PYREX**

For a listing of trademarks, visit us at www.corning.com/lifesciences/trademarks. All other trademarks in this document are the property of their respective owners.

© 2014 Thermo Fisher Scientific Inc. All rights reserved.
Trademarks used are owned as indicated at www.fishersci.com/trademarks.

In the United States:

For customer service, call 1-800-766-7000
To fax an order, use 1-800-926-1166
To order online: www.fishersci.com

In Canada:

For customer service, call 1-800-234-7437
To fax an order, use 1-800-463-2996
To order online: www.fishersci.ca



A Thermo Fisher Scientific Brand

BN0126153